PETERMANN-TECHNIK GmbH Lechwiesenstr. 13 • D-86899 • Landsberg am Lech Tel: +49/8191/305395 • Fax: +49/8191/305397 info@petermann-technik.com • www.petermann-technik.com



SMD QUARTZ CRYSTAL SPECIFICATION

SERIES "SMD03025/4 32.000 MHZ 10/20/-40+85/8PF"

FEATURES

- + Cheapest available miniature SMD-Crystal in ceramic package
- + High reliability for low cost
- + Optimized low ESR resonator design for fast oscillation start-up
- + Our top quality promise / depth of production:
 - Only use of crystal blanks from our in-house production Excellent product features guaranteed by multiple 100% tests 100% quality monitoring from crystal raw material to the end product



GENERAL DATA

PRODUCT FEATURES AND CONDITIONS
SMD03025/4
0.8 mm max.
32.000 MHz
AT-FUNDAMENTAL
$30~\Omega$ max.
±10 ppm
8 pF
-40/+85°C
±20 ppm over -40/+85°C (referred to +25°C)
2 pF max.
±10 ppm max. after 10 years
100 μW typ. / 200 μW max.
>500 MΩ DC/100V ±15V
-40/+125°C
0.3 ppb/G typ.
Tape & Reel (3.000 pcs)
Lead free and RoHS 2 compliant
See reflow solder profile
Line 1 = P328W2 Line 2 = xxxx (xxxx = date code)
SMD03025/4 32.000 MHz 10/20/-40+85/8pF
QEU9010928


Note:

- 1. The reference temperature for all specified values and tests is +25°C.
- 2. Do not use cleaning baths operating at ultrasonic frequencies or ultrasonic welding processes.







DIMENSIONS



REEL SPECIFICATION



REFLOW SOLDER PROFILE



IPC/JEDEC Standard	IPC/JEDEC J-STD-020
Moisture Sensitivity Level	Level 1
TS MAX to TL (Ramp-up Rate)	3°C/second Maximum
Preheat	
- Temperature Minimum (TS MIN)	150°C
- Temperature Typical (TS TYP)	175°C
- Temperature Maximum (TS MAX)	200°C
- Time (tS)	60 - 180 Seconds
Ramp-up Rate (TL to TP)	3°C/second Maximum
Time Maintained Above:	
- Temperature (TL)	217°C
- Time (TL)	60 - 150 Seconds
Peak Temperature (TP)	260°C Maximum
Target Peak Temperature (TP Target)	255°C
Time within 5°C of actual peak (tP)	20 - 40 seconds
Max. Number of Reflow Cycles	2
Ramp-down Rate	6°C/second Maximum
Time 25°C to Peak Temperature (t)	8 minutes Maximum

PETERMANN-TECHNIK GmbH Lechwiesenstr. 13 • D-86899 • Landsberg am Lech Tel: +49/8191/305395 • Fax: +49/8191/305397 info@petermann-technik.com • www.petermann-technik.com





PREMIUM QUALITY BY PETERMANN-TECHNIK



OUR COMPANY IS CERTIFIED ACCORDING TO ISO 9001:2015 IN OCTOBER 2016 BY THE DMSZ CERTIFIKATION GMBH AND CERTIFIED ACCORDING TO 14001:2015 IN MARCH 2018 BY SEQ-CERT.

THIS IS FOR YOU TO ENSURE THAT THE PRINCIPLES OF QUALITY MANAGEMENT ARE FULLY IMPLEMENTED IN OUR QUALITY MANAGEMENT SYSTEM AND QUALITY CONTROL METHODS ALSO DOMINATE OUR QUALITY STANDARDS.